



SmartForm TBS417

ZBS417 EP-T SI SET

TBS415 ACC, Silver

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. Energy efficiency. As well as incorporating energy-efficient LED or TL5 light sources and a range of Philips electronic ballasts, the SmartForm recessed family can be equipped with lighting controls for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense) in order to reduce energy consumption (W/m2 is very low). In this way, this Green Flagship range also reduces the overall cost of ownership as well as CO2 levels, making SmartForm an environmentally friendly choice. SmartForm recessed TBS417 – 'light line beam'. Slender SmartForm recessed continuous light-line luminaires are designed for integration in linear exposed T-bar and plaster ceilings. 'Light line beam' TBS417 1-lamp. Continuous light line for micro-optics, asymmetrical optic and rimless MLO and Opal covers. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 90 mm. 'Light line beam' TBS417 2-lamps. Continuous light line for mini-optics, 2-lamps. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 115 mm.

Product data

General Information	
Accessory color	Silver
Product family code	ZBS417 [TBS415 ACC]
Mechanical and Housing	
Housing Color	Silver

Product Data	
Order product name	ZBS417 EP-T SI SET
Full product name	ZBS417 EP-T SI SET
Full product code	871794398452799
Order code	910403205103
Material Nr. (12NC)	910403205103
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8717943984527
Numerator - Packs per outer box	20
EAN/UPC - Case	8717943984534

