



SmartForm TBS417

ZZS400 OCR OPTICAL COVER REMOVER

Smartform ACC.

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. Energy efficiency. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m^2 is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO₂ levels, making SmartForm an environmentally friendly choice. SmartForm recessed TBS417 – 'light line beam'. Slender SmartForm recessed continuous light-line luminaires are designed for integration in linear exposed T-bar and plaster ceilings. 'Light line beam' TBS417 1-lamp. Continuous light line for micro-optics, asymmetrical optic and rimless MLO and Opal covers. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 90 mm. 'Light line beam' TBS417 2-lamps. Continuous light line for mini-optics, 2-lamps. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 115 mm.

Product data

General Information			
Product family code	ZZS400 [Smartform ACC.]	Order code	98469599
		Material Nr. (12NC)	910403205603
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8717943984695
		Numerator - Packs per outer box	20
		EAN/UPC - Case	8717943984701
Product Data			
Order product name	ZZS400 OCR OPTICAL COVER REMOVER		
Full product name	ZZS400 OCR OPTICAL COVER REMOVER		
Full product code	871794398469599		

