



SmartForm TBS417

ZZS400 OCR OPTICAL COVER REMOVER

Smartform ACC.

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m² is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO2 levels, making SmartForm an environmentally friendly choice. Slender SmartForm recessed continuous light-line luminaires are designed for integration in linear exposed T-bar and plaster ceilings. Continuous light line for micro-optics, asymmetrical optic and rimless MLO and Opal covers. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 90 mm. Continuous light line for mini-optics, 2-lamps. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 115 mm.

Product data

General Information	
Product family code	ZZS400 [Smartform ACC.]
Product Data	
Order product name	ZZS400 OCR OPTICAL COVER REMOVER
Full product name	ZZS400 OCR OPTICAL COVER REMOVER
Full product code	871794398469599
Order code	910403205603

Material Nr. (12NC)	910403205603
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943984695
Numerator - Packs per outer box	20
EAN/UPC - Case	8717943984701