



# Tango MMF283

## MMF283 MHN-TD70W K 240V-50Hz S

MHN-TD, 70 W, Symmetrical

Compact, sturdy floodlight complete with integral gear, particularly suited for surface lighting using metal halide or high-pressure sodium lamps. All-weather construction designed for simple cleaning and speedy servicing.

### Product data

General Information	
Lamp family code	MHN-TD
Cap-Base	- [-]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optic type outdoor	Symmetrical
Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Power Consumption	70 W
Mechanical and Housing	
Housing Color	-

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	MMF283 MHN-TD70W K 240V-50Hz S
Full product name	MMF283 MHN-TD70W K 240V-50Hz S
Full product code	910403333201
Order code	910403333201
Material Nr. (12NC)	910403333201
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Tango MMF283

Dimensional drawing

