



# Tango MMF383

## MMF383 HPI-TP400W K 240V-50Hz S

MASTER HPI-T Plus, 400 W, Symmetrical

A compact and sturdy family of floodlights complete with integral gear, particularly suited for surface lighting using metal halide or high-pressure sodium lamps. Its all-weather construction is designed for simple cleaning and speedy servicing.

### Product data

General Information	
Lamp family code	HPI-TP [MASTER HPI-T Plus]
Cap-Base	E40 [E40]
Gear	HGR [HPL/HPI gear]
Light Technical	
Number of light sources	1
Optic type outdoor	Symmetrical
Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Power Consumption	400 W
Mechanical and Housing	
Housing Color	-

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	MMF383 HPI-TP400W K 240V-50Hz S
Full product name	MMF383 HPI-TP400W K 240V-50Hz S
Full product code	910403334401
Order code	910403334401
Material Nr. (12NC)	910403334401
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163181899
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163181899

## Tango MMF383

## Dimensional drawing

