



# Velocity

## SGP338 SON-T250W 220V GB ALU SD CN

SON-T, 250 W, 220 V, Glass bowl/cover, Aluminum

Road lighting luminaire for tubular high-pressure sodium lamps up to 400W. Step dimming option available up to SON-T 250W lamp version.

### Product data

General Information	
Lamp family code	SON-T [SON-T]
Cap-Base	E40 [E40]
Gear	SGR [SON gear]
Light Technical	
Number of light sources	1
Optical cover type	Glass bowl/cover
Optic type outdoor	Closed T-POT
Operating and Electrical	
Input Voltage	220 V
Power Consumption	250 W
Mechanical and Housing	
Housing Color	Aluminum

Approval and Application	
Ingress protection code	IP43/66 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof]
Product Data	
Order product name	SGP338 SON-T250W 220V GB ALU SD CN
Full product name	SGP338 SON-T250W 220V GB ALU SD CN
Full product code	910403364480
Order code	910403364480
Material Nr. (12NC)	910403364480
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Velocity

### Dimensional drawing

