



TCW060 C

TCW060 C 2xTL-D36W HF 220V

2, MASTER TL-D, 36 W, Electronic high-frequency, 220 V

Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.


Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HF [Electronic high-frequency]
Light Technical	
Number of light sources	2
Operating and Electrical	
Input Voltage	220 V
Power Consumption	36 W
Product Data	
Order product name	TCW060 C 2xTL-D36W HF 220V

Full product name	TCW060 C 2xTL-D36W HF 220V
Full product code	910403630029
Order code	910403630029
Material Nr. (12NC)	910403630029
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828687380
Numerator - Packs per outer box	6
EAN/UPC - Case	6923828698935

TCW060 C

Dimensional drawing



Product	A	B
TCW060 C 2xTL-D36W HF 220V	900 mm	1,270 mm

