



TCW060 C

TCW060 C 2xTL-D36W HF 220V

China - 2 pcs - MASTER TL-D - 36 W - Electronic high-frequency - 220 V


Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.

Product data

General Information		Order product name	
Duplication code	C [China]	TCW060 C 2xTL-D36W HF 220V	
Number of light sources	2 [2 pcs]	EAN/UPC – product	6923828687380
Lamp family code	TL-D [MASTER TL-D]	Order code	910403630029
Lamp power	36 W	Numerator – quantity per pack	1
Gear	HF [Electronic high-frequency]	Numerator – packs per outer box	6
Operating and Electrical		Material no. (12NC)	910403630029
Input voltage	220 V	Net weight (piece)	2.290 kg
Product Data			
Full product code	910403630029		

TCW060 C

Dimensional drawing



TCW060 C

