



TCW060 C

TCW060 C 2xTL-D36W HF 220V

China - 2 pcs - MASTER TL-D - 36 W - Electronic high-frequency - 220 V

Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.


Product data

General Information	
Duplication code	C [China]
Number of light sources	2 [2 pcs]
Lamp family code	TL-D [MASTER TL-D]
Lamp power	36 W
Gear	HF [Electronic high-frequency]
Operating and Electrical	
Input voltage	220 V
Mechanical and Housing	
Dimensions (height x width x depth)	NaN x NaN x NaN mm (NaN x NaN x NaN in)

Product Data	
Full product code	910403630029
Order product name	TCW060 C 2xTL-D36W HF 220V
EAN/UPC – product	6923828687380
Order code	03630029
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	910403630029
Net weight (piece)	2.290 kg

TCW060 C

Dimensional drawing



TCW060 C

