



# TCW060 C

## TCW060 C 1xTL5-28W HF 220V

1, TL5, 28 W, Electronic high-frequency, 220 V

Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.


### Product data

<b>General Information</b>	
Lamp family code	TL5 [TL5]
Gear	HF [Electronic high-frequency]
<b>Light Technical</b>	
Number of light sources	1
<b>Operating and Electrical</b>	
Input Voltage	220 V
Power Consumption	28 W
<b>Product Data</b>	
Order product name	TCW060 C 1xTL5-28W HF 220V

Full product name	TCW060 C 1xTL5-28W HF 220V
Full product code	910403630030
Order code	910403630030
Material Nr. (12NC)	910403630030
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828687397
Numerator - Packs per outer box	12
EAN/UPC - Case	6923828698942

TCW060 C

Dimensional drawing



Product	A	B
TCW060 C 1xTL5-28W HF 220V	800 mm	1,215 mm

