



# Celino TPS680 C

## TPS682 C 1xTL5-35W HFP D8 FU SM2 ALU

1, TL5, 35 W, HF Performer, Semi-high-gloss optic 3D micro-lamellae, Fuse included, Aluminum

Celino is a complete luminaire range that reflects the market trend towards miniaturization and architectural integration, while at the same time delivering a significant advance in optical performance. Celino features Philips' aluminum micro optic with 3D lamellae, which ensures optimum visual comfort and efficiency in compliance with the latest office-lighting norm (EN 12464-1). Made of natural anodized aluminum, the housing of Celino is a mere 71 mm wide and has die-cast-aluminum end caps. The design allows multiple luminaires to be connected in a line arrangement. Celino is available as a full range – suspended, surface-mounted, free-standing, recessed and wall-mounted – for maximum freedom in application.


### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFP [HF Performer]
Light Technical	
Number of light sources	1
Optic type	Semi-high-gloss optic 3D micro-lamellae
Optical cover type	-
Operating and Electrical	
Power Consumption	35 W
Mechanical and Housing	
Housing Color	Aluminum

Product Data	
Order product name	TPS682 C 1xTL5-35W HFP D8 FU SM2 ALU
Full product name	TPS682 C 1xTL5-35W HFP D8 FU SM2 ALU
Full product code	910403630070
Order code	910403630070
Material Nr. (12NC)	910403630070
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

# Celino TPS680 C

## Dimensional drawing



Product	A	B
TPS682 C 1xTL5-35W HFP D8 FU SM2 ALU	1,520 mm	1,420 mm

