



Smart Halogen Downlight QBS020

QBS022 1x MAX50W/12V-GU5.3 WH

1, GU5.3, 白色

Shop owners opening a new outlet or refurbishing their current installation and contractors looking for attractive propositions for their customers (small/non-chain retailers) now have the ideal solution for impactful, yet affordable accent lighting. Our Smart Halogen Downlight offers customers a choice of different shapes to suit different functions, and the professional finish lends the luminaire an air of contemporary sophistication. Thanks to its robust housing, the Smart Halogen Downlight is a long-lasting solution. Quality clips ensure ease of installation.

产品数据

一般資訊	
燈座基底	GU5.3 [GU5.3]
照明技術	LED
照明技術	
光源數	1
燈具光束擴散	108°
運轉與電力	
輸入電壓	12 V
線路頻率	50 to 60 Hz
輸入頻率	50 至 60 Hz

溫度	
環境溫度範圍	-10 至 +35 °C
機械與外罩	
外罩色彩	白色
整體長度	85 mm
整體寬度	300 mm
整體高度	300 mm
尺寸 (高 x 寬 x 深)	300 x 300 x 85 mm
認證與應用	
防水防塵規範 (IP)	IP20 [可防止手指侵入]
機械衝擊保護規範	IK03 [0.3 J]
保護等級 IEC	安全等級 II

Smart Halogen Downlight QBS020

產品資料	
下訂產品名稱	QBS022 1x MAX50W/12V-GU5.3 WH
完整產品名稱	QBS022 1x MAX50W/12V-GU5.3 WH
完整產品代碼	910403630259
訂單代碼	910403630259
材質 Nr. (12NC)	910403630259

分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	6923828687458
分子 - 每一外盒包裝	50
EAN/UPC - 箱	6923828699000

二维绘图

