



# Smart Halogen Downlight QBS020

QBS024 1x MAX50W/12V-GU5.3 GR

1, GU5.3, Grey

Shop owners opening a new outlet or refurbishing their current installation and contractors looking for attractive propositions for their customers (small/non-chain retailers) now have the ideal solution for impactful, yet affordable accent lighting. Our Smart Halogen Downlight offers customers a choice of different shapes to suit different functions, and the professional finish lends the luminaire an air of contemporary sophistication. Thanks to its robust housing, the Smart Halogen Downlight is a long-lasting solution. Quality clips ensure ease of installation.

## Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Lighting Technology	LED
Light Technical	
Number of light sources	1
Luminaire light beam spread	108°
Operating and Electrical	
Input Voltage	12 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Temperature	
Ambient temperature range	-10 to +35 °C
Mechanical and Housing	
Housing Color	Grey
Overall length	37 mm
Overall width	225 mm
Overall height	225 mm
Dimensions (Height x Width x Depth)	225 x 225 x 37 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II

# Smart Halogen Downlight QBS020

Product Data	
Order product name	QBS024 1x MAX50W/12V-GU5.3 GR
Full product name	QBS024 1x MAX50W/12V-GU5.3 GR
Full product code	910403630264
Order code	910403630264
Material Nr. (12NC)	910403630264

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828687502
Numerator - Packs per outer box	50
EAN/UPC - Case	6923828699055

## Dimensional drawing

