



# Smart Halogen Downlight QBS020

## QBS041 1xMAX50W/12V-GU5.3 WH

1, GU5.3, White

Shop owners opening a new outlet or refurbishing their current installation and contractors looking for attractive propositions for their customers (small/non-chain retailers) now have the ideal solution for impactful, yet affordable accent lighting. Our Smart Halogen Downlight offers customers a choice of different shapes to suit different functions, and the professional finish lends the luminaire an air of contemporary sophistication. Thanks to its robust housing, the Smart Halogen Downlight is a long-lasting solution. Quality clips ensure ease of installation.

### Product data

|                                 |               |                                     |                         |
|---------------------------------|---------------|-------------------------------------|-------------------------|
| <b>General Information</b>      |               | <b>Temperature</b>                  |                         |
| Cap-Base                        | GU5.3 [GU5.3] | Ambient temperature range           | -10 to +35 °C           |
| Lighting Technology             | LED           | <b>Mechanical and Housing</b>       |                         |
| <b>Light Technical</b>          |               | Housing Color                       | White                   |
| Number of light sources         | 1             | Overall length                      | 37 mm                   |
| Luminaire light beam spread     | 108°          | Overall width                       | 225 mm                  |
| <b>Operating and Electrical</b> |               | Overall height                      | 225 mm                  |
| Input Voltage                   | 12 V          | Dimensions (Height x Width x Depth) | 225 x 225 x 37 mm       |
| Line Frequency                  | 50 to 60 Hz   | <b>Approval and Application</b>     |                         |
| Input Frequency                 | 50 to 60 Hz   | Ingress protection code             | IP20 [Finger-protected] |
|                                 |               | Mech. impact protection code        | IK03 [0.3 J]            |
|                                 |               | Protection class IEC                | Safety class II         |

# Smart Halogen Downlight QBS020

| Product Data        |                              |
|---------------------|------------------------------|
| Order product name  | QBS041 1xMAX50W/12V-GU5.3 WH |
| Full product name   | QBS041 1xMAX50W/12V-GU5.3 WH |
| Full product code   | 910403630289                 |
| Order code          | 910403630289                 |
| Material Nr. (12NC) | 910403630289                 |

|                                 |               |
|---------------------------------|---------------|
| Numerator - Quantity Per Pack   | 1             |
| EAN/UPC - Product/Case          | 6923828687724 |
| Numerator - Packs per outer box | 30            |
| EAN/UPC - Case                  | 6923828699277 |

## Dimensional drawing

