



Basic Modular LBX300

LBX300 1xMAX50W/12V-GU5.3 WH

白色

Our Smart Modular Downlight is an affordable, reliable and flexible solution designed to deliver both general and accent lighting in retail environments. Driven by electronic and electromagnetic gear, the trendy Smart Modular Downlight combines an attractive visual appearance with ease of installation and maintenance. A robust housing and high-quality components ensure the product's long lifetime.

产品数据

一般資訊		功率因數 (比值)	
光源可更換	無		0.8
部件	-	溫度	
照明技術	LED	環境溫度範圍	0 至 +35 °C
照明技術		機械與外罩	
光通量	300 lm	外殼材質	塑膠
相關色彩溫度 (規範)	4000 K	反光層材質	聚碳酸酯
演色性指數 (CRI)	80	外罩色彩	白色
光源色彩	3000/4000/6500	整體長度	225 mm
燈具光束擴散	110°	整體寬度	225 mm
運轉與電力		整體高度	225 mm
線路頻率	50 or 60 Hz	整體直徑	225 mm
輸入頻率	50 或 60 Hz	尺寸 (高 x 寬 x 深)	225 x 225 x 225 mm
耗電量	4 W	認證與應用	
		防水防塵規範 (IP)	IP20 [可防止手指侵入]

Basic Modular LBX300

機械衝擊保護規範	IK02 [0.2 J 標準]
保護等級 IEC	安全等級 II
產品資料	
下訂產品名稱	LBX300 1xMAX50W/12V-GU5.3 WH
完整產品名稱	LBX300 1xMAX50W/12V-GU5.3 WH
完整產品代碼	910403630425
訂單代碼	910403630425

材質 Nr. (12NC)	910403630425
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	6923828688189
分子 - 每一外盒包裝	8
EAN/UPC - 箱	6923828699734

二维绘图

