



# Basic Modular LBX300

LBX300 1xMAX50W/12V-GU5.3 WH

White

Our Smart Modular Downlight is an affordable, reliable and flexible solution designed to deliver both general and accent lighting in retail environments. Driven by electronic and electromagnetic gear, the trendy Smart Modular Downlight combines an attractive visual appearance with ease of installation and maintenance. A robust housing and high-quality components ensure the product's long lifetime.

## Product data

<b>General Information</b>		<b>Power Factor (Fraction)</b>	
Light source replaceable	No	0.8	
Gear	-	<b>Temperature</b>	
Lighting Technology	LED	Ambient temperature range	
<b>Light Technical</b>		0 to +35 °C	
Luminous Flux	300 lm	<b>Mechanical and Housing</b>	
Correlated Color Temperature (Nom)	4000 K	Housing Material	
Color rendering index (CRI)	80	Plastic	
Light source color	3000/4000/6500	Reflector material	
Luminaire light beam spread	110°	Polycarbonate	
<b>Operating and Electrical</b>		Housing Color	
Line Frequency	50 or 60 Hz	White	
Input Frequency	50 or 60 Hz	Overall length	
Power Consumption	4 W	225 mm	
		Overall width	
		225 mm	
		Overall height	
		225 mm	
		Overall diameter	
		225 mm	
		Dimensions (Height x Width x Depth)	
		225 x 225 x 225 mm	
		<b>Approval and Application</b>	
		Ingress protection code	
		IP20 [Finger-protected]	

# Basic Modular LBX300

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Product Data	
Order product name	LBX300 1xMAX50W/12V-GU5.3 WH
Full product name	LBX300 1xMAX50W/12V-GU5.3 WH
Full product code	910403630425
Order code	910403630425

Material Nr. (12NC)	910403630425
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828688189
Numerator - Packs per outer box	8
EAN/UPC - Case	6923828699734

## Dimensional drawing

