



Basic Modular LBX300

LBX300 2xMAX50W/12V-GU5.3 GR

灰色

Our Smart Modular Downlight is an affordable, reliable and flexible solution designed to deliver both general and accent lighting in retail environments. Driven by electronic and electromagnetic gear, the trendy Smart Modular Downlight combines an attractive visual appearance with ease of installation and maintenance. A robust housing and high-quality components ensure the product's long lifetime.

产品数据

一般資訊	
光源可更換	無
部件	-
照明技術	LED
照明技術	
光通量	300 lm
相關色彩溫度 (規範)	4000 K
演色性指數 (CRI)	80
光源色彩	3000/4000/6500
燈具光束擴散	110°
運轉與電力	
線路頻率	50 or 60 Hz
輸入頻率	50 或 60 Hz
耗電量	4 W

功率因數 (比值)	0.8
溫度	
環境溫度範圍	0 至 +35 °C
機械與外罩	
外殼材質	塑膠
反光器材質	聚碳酸酯
外罩色彩	灰色
整體長度	225 mm
整體寬度	225 mm
整體高度	225 mm
整體直徑	225 mm
尺寸 (高 x 寬 x 深)	225 x 225 x 225 mm
認證與應用	
防水防塵規範 (IP)	IP20 [可防止手指侵入]

Basic Modular LBX300

機械衝擊保護規範	IK02 [0.2 J 標準]
保護等級 IEC	安全等級 II
產品資料	
下訂產品名稱	LBX300 2xMAX50W/12V-GU5.3 GR
完整產品名稱	LBX300 2xMAX50W/12V-GU5.3 GR
完整產品代碼	910403630428
訂單代碼	910403630428

材質 Nr. (12NC)	910403630428
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	6923828688219
分子 - 每一外盒包裝	6
EAN/UPC - 箱	6923828699765

二维绘图

