



Basic Modular LBX300

LBX300 3xMAX50W/12V-GU5.3 GR

Grey

Our Smart Modular Downlight is an affordable, reliable and flexible solution designed to deliver both general and accent lighting in retail environments. Driven by electronic and electromagnetic gear, the trendy Smart Modular Downlight combines an attractive visual appearance with ease of installation and maintenance. A robust housing and high-quality components ensure the product's long lifetime.

Product data

General Information	
Light source replaceable	No
Gear	-
Lighting Technology	LED

Light Technical	
Luminous Flux	300 lm
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	80
Light source color	3000/4000/6500
Luminaire light beam spread	110°

Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	4 W

Power Factor (Fraction)	0.8
-------------------------	-----

Temperature	
Ambient temperature range	0 to +35 °C

Mechanical and Housing	
Housing Material	Plastic
Reflector material	Polycarbonate
Housing Color	Grey
Overall length	225 mm
Overall width	225 mm
Overall height	225 mm
Overall diameter	225 mm
Dimensions (Height x Width x Depth)	225 x 225 x 225 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Basic Modular LBX300

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Product Data	
Order product name	LBX300 3xMAX50W/12V-GU5.3 GR
Full product name	LBX300 3xMAX50W/12V-GU5.3 GR
Full product code	910403630430
Order code	910403630430

Material Nr. (12NC)	910403630430
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828688233
Numerator - Packs per outer box	6
EAN/UPC - Case	6923828699789

Dimensional drawing

