



# Basic HID MBS070

## MBS070 1xCDM-R30-70W H WH

1, MASTERColour CDM-R PAR-30, 70 W, External gear box, White

Our Smart HID downlight is a reliable and flexible solution offering a variety of designs with CDM lamps driven by electromagnetic or electronic gear. With its high lumen output, high energy efficacy, high color rendering index and tight focus, Smart HID downlight is ideally suited to accent lighting in shops or hotels. Its elegant design guarantees a perfect fit in any retail or hospitality environment. And because the housing is adjustable and rotatable, installation couldn't be any simpler.

### Product data

General Information	
Lamp family code	CDM-R30 [MASTERColour CDM-R PAR-30]
Gear	H [External gear box]
Light Technical	
Number of light sources	1
Operating and Electrical	
Power Consumption	70 W
Mechanical and Housing	
Housing Color	White

Product Data	
Order product name	MBS070 1xCDM-R30-70W H WH
Full product name	MBS070 1xCDM-R30-70W H WH
Full product code	910403630447
Order code	910403630447
Material Nr. (12NC)	910403630447
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828688462
Numerator - Packs per outer box	8
EAN/UPC - Case	6923828601201

## Basic HID MBS070

### Dimensional drawing

