



Theta FBS110

FBS115 MAX18W-E27 220V

E27, 220 V

Our Smart CFL-I downlight is a safe, reliable and flexible solution that comes in five sizes for different cut-outs. Its elegant design guarantees a perfect fit in any retail or hospitality environment. And because the downlight has been designed specifically for CFL-I lamps, installation and maintenance couldn't be any simpler.

Product data

General Information	
Cap-Base	E27 [E27]
Gear	-
Lighting Technology	LED
Light Technical	
Number of light sources	1
Luminaire light beam spread	108°
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Temperature	
Ambient temperature range	-10 to +35 °C
Mechanical and Housing	
Housing Color	White
Overall length	85 mm
Overall width	300 mm

Overall height	300 mm
Dimensions (Height x Width x Depth)	300 x 300 x 85 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II

Product Data	
Order product name	FBS115 MAX18W-E27 220V
Full product name	FBS115 MAX18W-E27 220V
Full product code	910403630462
Order code	910403630462
Material Nr. (12NC)	910403630462
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828688578
Numerator - Packs per outer box	12
EAN/UPC - Case	6923828601317

Theta FBS110

Dimensional drawing

