



Intelligent Sereno TBS869/528

TBS869 C 1x28W/840 HFP WV D8-H FTB CAU

1, 28 W, Electronic Primalume, Semi-high-gloss optic 3D micro-lamellae high reflectance, Fused terminal block, Cord with plug SAA 3-pole

Customers want green buildings in order to save energy, reduce running costs and enhance their sustainability credentials. Intelligent Sereno is a TL5 recessed luminaire family, which integrates intelligent daylight linking and presence detection for automatic energy saving. At the same time, its advanced optical technology maintains the quality of light at the office norm level.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EBP [Electronic Primalume]
Embedded control	-
Light Technical	
Number of light sources	1
Light source color	-
Optic type	Semi-high-gloss optic 3D micro-lamellae high reflectance
Operating and Electrical	
Power Consumption	28 W
Cable	Cord with plug SAA 3-pole

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	TBS869 C 1x28W/840 HFP WV D8-H FTB CAU
Full product name	TBS869 C 1x28W/840 HFP WV D8-H FTB CAU
Full product code	910403630652
Order code	910403630652
Material Nr. (12NC)	910403630652
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Intelligent Sereno TBS869/528

Dimensional drawing

