



# Cozy TMS018 C

## TMS018 C 2xTL-D36W IC R

2, MASTER TL-D, 36 W, Conventional, Reflector

Our Smart T8 Batten is an affordable, reliable and flexible solution designed to deliver both general and accent lighting in retail environments. Driven by electronic and electromagnetic gear, the trendy Smart Modular Downlight combines an attractive visual appearance with ease of installation and maintenance. A robust housing and high-quality components ensure the product's long lifetime.

### Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	2
Optic type	Reflector
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	36 W
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Protection class IEC	Safety class I
Product Data	
Order product name	TMS018 C 2xTL-D36W IC R
Full product name	TMS018 C 2xTL-D36W IC R
Full product code	910403630714
Order code	910403630714
Material Nr. (12NC)	910403630714
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828602499
Numerator - Packs per outer box	6
EAN/UPC - Case	6923828602499

## Cozy TMS018 C

### Dimensional drawing

