



# OptiVision MVP507

## MVP507 MHN-LA2000W/956 400V WB SI SL

OPTIVISION, MASTER MHN-LA, 2000 W, Wide beam

OptiVision is an asymmetric downlighting luminaire that combines compact dimensions with very high efficiency. Available with narrow, medium and wide beams for flexibility in application, it provides excellent control of spill light and limitation of glare and upward leakage of light. OptiVision can accommodate metal-halide lamps for good color rendering or high-pressure sodium lamps for economical operation. Excellent spill-light control, limitation of glare and upward leakage of light is secured by asymmetric optics that achieve peak intensity at 60° and a sharp cut-off of light at 80°. The MHN-LA/FC lamps guarantee pleasant and natural color rendering and comfortable atmosphere.

### Product data

General Information		Color rendering index (CRI)	
Lamp family code	MHN-LA [MASTER MHN-LA]	Color rendering index (CRI)	>90
Number of gear units	-	Number of light sources	1
Gear	-	Light source color	956 daylight
Product family code	MVP507 [OPTIVISION]	Optical cover type	Flat glass
Value ladder	Specification	Luminaire light beam spread	-
CE mark	Yes	Optic type outdoor	Wide beam
Warranty period	1 years	<b>Operating and Electrical</b>	
Flammability mark	-	Input Voltage	400 V
ENEC mark	-	Line Frequency	50 to 60 Hz
EU RoHS compliant	Yes	Power Consumption	2,000 W
		Connection	Screw connector
		Cable	-
<b>Light Technical</b>			
Standard tilt angle posttop	-		
Standard tilt angle side entry	-		
Correlated Color Temperature (Nom)	5600 K		

# OptiVision MVP507

## Temperature

Ambient temperature range	-30 to +35 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	No
Control interface	-
Constant light output	No

## Mechanical and Housing

Housing Material	Aluminum
Reflector material	Aluminum
Optic material	Aluminum
Optical cover material	-
Fixation material	Steel
Housing Color	Aluminum
Mounting device	Mounting bracket adjustable
Optical cover shape	-
Optical cover finish	-
Overall height	386 mm
Effective projected area	0.16 m <sup>2</sup>

## Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
-------------------------	--

Mech. impact protection code	IK08 [5 J vandal-protected]
------------------------------	-----------------------------

Surge Protection (Common/Differential)	-
--	---

Sustainability rating	-
-----------------------	---

Protection class IEC	Safety class I
----------------------	----------------

## Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

## Product Data

Order product name	MVP507 MHN-LA2000W/956 400V WB SI SL
--------------------	--------------------------------------

Full product name	MVP507 MHN-LA2000W/956 400V WB SI SL
-------------------	--------------------------------------

Full product code	872790029712600
-------------------	-----------------

Order code	29712600
------------	----------

Material Nr. (12NC)	910403787812
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

EAN/UPC - Product/Case	8727900297126
------------------------	---------------

Numerator - Packs per outer box	1
---------------------------------	---

EAN/UPC - Case	8727900297126
----------------	---------------

## Dimensional drawing

