



# ComfortVision SNF111

## SNF111 2xSON-T400W K MB SI

COMFORTVISION, 2, SON-T, 400 W, Medium beam

ComfortVision is a high-efficiency, asymmetric floodlight, distributing a low-glare beam evenly and accurately. It can accommodate metal-halide lamps for good color rendering or a high-pressure sodium lamp for economical performance. Available in medium- or narrow-beam versions, the floodlight accepts a single 1000 or two 400 or 600 W lamps. The twin-lamp version offers switching flexibility that permits tailoring to the user's needs while allowing energy savings. ComfortVision's rugged all-weather construction is designed for easy aiming, simple cleaning and speedy servicing. For optimal downlighting, the luminaire should be mounted horizontally at a height of 15–25 meters. It has an adjustment range of  $\pm 12^\circ$  from the horizontal. A universal mounting bracket allows mounting to headframes, ceilings and walls.

### Product data

General Information		Approval and Application	
Lamp family code	SON-T [SON-T]	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Gear	CONV [Conventional]	Protection class IEC	Safety class I
Product family code	SNF111 [COMFORTVISION]	Product Data	
CE mark	Yes	Order product name	SNF111 2xSON-T400W K MB SI
ENEC mark	-	Full product name	SNF111 2xSON-T400W K MB SI
Light Technical		Full product code	871829141642500
Number of light sources	2	Order code	910403929812
Optic type outdoor	Medium beam	Material Nr. (12NC)	910403929812
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	400 W	EAN/UPC - Product/Case	8718291416425
		Numerator - Packs per outer box	1
		EAN/UPC - Case	8718291416425

Dimensional drawing

