



Europa 2

FBS120 2XPL-C/4P18W/840 HF-H P CCE

EUROPA 2, 2, MASTER PL-C 4 Pin, 18 W, 840 neutral white, Electronic high-frequency in external gear box (HF), Prismatic refractor, Cable with CEE 7 plug 3-pole

New Europa 2 fixed recessed downlights for compact fluorescent PL-C lamps with automatic fixing clips ensuring quick and easy installation and highly efficient improved optics. Available in three formats: FBS120, FBS120 HF and FBS122. Equipped with either a prismatic light control panel, an opal cover, a clear front panel or a glare control louvre. Available in a ready-to-install kit version, with premounted lamps and a preconnected cable with a Wieland “quick connector”.

Product data

General Information	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]
Gear	HF-H [Electronic high-frequency in external gear box (HF)]
Product family code	FBS120 [EUROPA 2]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	-
Optical cover type	Prismatic refractor

Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	18 W
Connection	-
Cable	Cable with CEE 7 plug 3-pole
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class II
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	FBS120 2XPL-C/4P18W/840 HF-H P CCE
Full product name	FBS120 2XPL-C/4P18W/840 HF-H P CCE

Europa 2

Full product code	871829108594200
Order code	08594200
Material Nr. (12NC)	910500451717
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291085942

Numerator - Packs per outer box 1	
EAN/UPC - Case	8718291085942

Dimensional drawing

