



GreenSpace

DN460B LED11S/840 PSU-E C ELP3 WH

150mm, LED Module, system flux 1100 lm, 840 neutral white,
Power supply unit DC compatible, external, Emergency lighting
3 hours duration, White RAL 9003

GreenSpace is a perfect solution where customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime while they are covering multiple applications. GreenSpace features the latest LED technology which enables extremely low power consumption. With its perfect fit you'll get the LED downlight that always fits and looks perfect at the same time. This perfect fit is available for cut out sizes from 150 to 280 mm. GreenSpace is designed for Circular Economy with optimized performance, extended lifetime through upgradability and integration options, ease of customization, recycling and disassembly. Housing and rim are made from production waste of polycarbonate sheets that are retrieved from swimming pools, car ports and illuminated advertising. And the product's long lifetime makes it a true 'fit and forget' solution.

Product data

General Information			
Lamp family code	LED11S [LED Module, system flux 1100 lm]		
Cap-Base	- [-]		
Light source replaceable	No		
Number of gear units	1 unit		
Gear	-		
Driver included	Yes		
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen		
			maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Product family code	DN460B [150mm]		
Lighting Technology	LED		
Value ladder	Specification		
CE mark	Yes		
Warranty period	5 years		
Flammability mark	For mounting on normally flammable surfaces		
ENEC mark	ENEC mark		

Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	1,200 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	109.09 lm/W
Color rendering index (CRI)	80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	High-gloss mirror
Luminaire light beam spread	80°
Unified glare rating CEN	22

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	14 A
Inrush time	0.24 ms
Power Consumption	11 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	30

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit DC compatible, external
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	-

Fixation material	-
Housing Color	White RAL 9003
Optical cover finish	-
Overall height	77 mm
Overall diameter	166 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM<3
Power consumption tolerance	+/-5%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* L90	50000 h
Lumen maintenance at median useful life* L80	100000 h

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	DN460B LED11S/840 PSU-E C ELP3 WH
Full product name	DN460B LED11S/840 PSU-E C ELP3 WH
Full product code	871869624318300
Order code	910500454947
Material Nr. (12NC)	910500454947
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696243183
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696243183

Dimensional drawing

