



GreenSpace

DN471B LED20S/830 PSD-E C ELP3 WH

200mm + anti-glare ring, LED Module, system flux 2000 lm, 830 warm white, Power supply unit with DALI interface, DC-compatible, external, Emergency lighting: three-hour duration, White RAL 9003

Customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime. GreenSpace is a cost-efficient and sustainable downlight that can be used to replace conventional CFL downlights in general lighting applications. It features the latest LED technology, which enables extremely low power consumption, while delivering consistent light output, stable colour performance and high colour rendering. The product's long lifetime makes it a true 'fit and forget' solution.

Product data

General Information			
Lamp family code	LED20S [LED Module, system flux 2000 lm]		useful life (B50) value also represents the B10 value.
Cap base	- [-]	Product family code	DN471B [200mm + anti-glare ring]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	Unit	Value ladder	Specification
Gear	-	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median		
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	Yes

Light Technical

Luminous Flux	2,150 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	115.59 lm/W
Colour rendering index (CRI)	80
Beam angle of light source	120 degree(s)
Light source colour	830 warm white
Optic type	High-gloss mirror
Luminaire light beam spread	64°
Unified Glare Rating (CEN)	19

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	16 A
Inrush time	0.22 ms
Power Consumption	18.6 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC-compatible, external
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	-
Fixation material	-
Housing Colour	White RAL 9003

Optical cover/lens finish	-
Overall height	95 mm
Overall diameter	216 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.44, 0.40) SDCM<3
Power consumption tolerance	+/-5%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L90
Lumen maintenance at median useful life* 100,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	DN471B LED20S/830 PSD-E C ELP3 WH
Full product name	DN471B LED20S/830 PSD-E C ELP3 WH
Full EOC	871869624353400
Order code	24353400
Material no. (12 NC)	910500454982
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696243534
Numerator – packs per outer box	1
EAN/UPC - Case	8718696243534

Dimensional drawing

