



# GreenSpace

## DN471B LED20S/830 PSED-VLC-E C ELP3 WH

200mm + anti-glare ring, LED Module, system flux 2000 lm, 830 warm white, Power supply unit with DALI interface, DC compatible, external, Emergency lighting 3 hours duration, Connection unit 5-pole, White RAL 9003

GreenSpace is a perfect solution where customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime while they are covering multiple applications. GreenSpace features the latest LED technology which enables extremely low power consumption. With its perfect fit you'll get the LED downlight that always fits and looks perfect at the same time. This perfect fit is available for cut out sizes from 150 to 280 mm. GreenSpace is designed for Circular Economy with optimized performance, extended lifetime through upgradability and integration options, ease of customization, recycling and disassembly. Housing and rim are made from production waste of polycarbonate sheets that are retrieved from swimming pools, car ports and illuminated advertising. And the product's long lifetime makes it a true 'fit and forget' solution.

### Product data

General Information	
Lamp family code	LED20S [LED Module, system flux 2000 lm]
Cap-Base	- [-]
Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper “Evaluating performance of LED based luminaires - January 2018”: statistically there

	is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Service tag	Yes
Product family code	DN471B [200mm + anti-glare ring]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years

Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes

#### Light Technical

Luminous Flux	2,150 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	115.59 lm/W
Color rendering index (CRI)	80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	High-gloss mirror
Luminaire light beam spread	64°
Unified glare rating CEN	19

#### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	16 A
Inrush time	0.22 ms
Power Consumption	18.6 W
Power Factor (Fraction)	0.9
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

#### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible, external
Control interface	DALI
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate

Optical cover material	-
Fixation material	-
Housing Color	White RAL 9003
Optical cover finish	-
Overall height	95 mm
Overall diameter	216 mm

#### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.44, 0.40) SDCM<3
Power consumption tolerance	+/-5%

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L80

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

#### Product Data

Order product name	DN471B LED20S/830 PSED-VLC-E C ELP3 WH
Full product name	DN471B LED20S/830 PSED-VLC-E C ELP3 WH
Full product code	871869624713600
Order code	910500456302
Material Nr. (12NC)	910500456302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696247136
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696247136

## Dimensional drawing

