



# GreenSpace Accent, elbow

## RS342B LED39S/840 PSU-E WB SI

GreenSpace Accent Elbow, LED Module, system flux 3500 lm, 840 neutral white, Power supply unit external (On/Off), Wide beam, Safety class II, Silver

Lighting is one of the key assets that can help retailers and building operators achieve their cost targets. Until now, many have been reluctant to switch from CDM to LED technology because the efficiency, initial investment, installation process, light level and/or quality of light of new LED solutions were not on par with their CDM existing solutions. This is no longer the case, thanks to GreenSpace Accent. Now, retailers and building operators can make the switch and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings compared to their existing CDM installation – all for a reasonable initial investment. And GreenSpace Accent's regular cut-out makes retrofit installation quick and easy. For food and fashion retailers, GreenSpace Accent elbow is also available with special light recipes to further enhance the store ambiance and to show the produce and goods on offer in the very best light: Fresh Food Champagne is the perfect LED solution for displaying fruit, vegetables, cheese, bread and pastries in a warm lighting ambiance; Fresh Food Meat creates the best light setting for meat enhancement in a cool natural ambiance; CrispWhite is the clear choice for fashion retailers to make colors appear rich and intense while keeping whites bright.

### Warnings and Safety

- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

### Product data

## GreenSpace Accent, elbow

<b>General Information</b>	
Lamp family code	LED35S [LED Module, system flux 3500 lm]
Cap base	- [-]
Light source replaceable	No
Number of gear units	Unit
Gear	-
Driver included	Yes
Remarks	* – According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Product family code	RS342B [GreenSpace Accent Elbow]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes
<b>Light Technical</b>	
Luminous Flux	3,800 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	120.63492063492063 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	840 neutral white
Optic type	Wide beam
Optical cover type	Acrylic bowl/cover clear
Luminaire light beam spread	36°
<b>Operating and Electrical</b>	
Input Voltage	220–240 V
Line Frequency	50 to 60 Hz
Inrush current	18.6 A
Inrush time	0.24 ms
Power Consumption	31.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	34
<b>Temperature</b>	
Ambient temperature range	+10 to +40 °C
<b>Controls and Dimming</b>	
Dimmable	No

Driver/power unit/transformer	Power supply unit external (On/Off)
Control interface	-
Constant light output	No
<b>Mechanical and Housing</b>	
Housing material	Aluminium
Reflector material	Aluminium and polycarbonate
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Polyamide
Housing Colour	Silver
Optical cover/lens finish	Clear
Overall length	228 mm
Overall width	193 mm
Overall height	156 mm
Overall diameter	193 mm
Dimensions (height x width x depth)	156 x 193 x 228 mm
<b>Approval and Application</b>	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM<3
Power consumption tolerance	+/-10%
<b>Over Time Performance (IEC Compliant)</b>	
Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80
<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	No
<b>Product Data</b>	
Order product name	RS342B LED39S/840 PSU-E WB SI
Full product name	RS342B LED39S/840 PSU-E WB SI
Full EOC	871869625535300
Order code	25535300
Material no. (12 NC)	910500456547
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696255353
Numerator – packs per outer box	1
EAN/UPC - Case	8718696255353

## GreenSpace Accent, elbow

### Dimensional drawing

