



Maxos LED Spot Inserts

4MX960 1 ST540C LED25S/830 PSU MB WH

MAXOS LED Spot Inserts - 1 unit - ST540C - LED Module, system flux 2500 lm - 830 warm white - Power supply unit - Medium beam - White

In specific areas of shops such as fruit and vegetable displays, projectors are often required in addition to LED-based general lighting. Accent lighting is an integral part of the Maxos concept. These dedicated inserts allow light lines to be flexibly equipped with the latest range of projectors as well as general LED lighting. 4MX960 units with projectors for Maxos trunkings with flat ribbon cable (5 x 2.5 mm, 7 x 2.5 mm) are available. These units can be clicked into the trunking sections like a regular electrical unit. Surface-mounted projectors are fixed to the inserts.

Product data

General Information		Product Family Code	
Number of units	1 unit	Product Family Code	4MX960 [MAXOS LED Spot Inserts]
Product family code unit A	ST540C	Unified glare rating CEN	Not applicable
Lamp family code	LED25S [LED Module, system flux 2500 lm]	Operating and Electrical	
Light source colour	830 warm white	Input voltage	220 to 240 V
Driver/power unit/transformer	PSU [Power supply unit]	Input frequency	50 to 60 Hz
Optic type	MB [Medium beam]	Controls and Dimming	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.	Dimmable	No

Maxos LED Spot Inserts

Mechanical and Housing

Colour White

Initial Performance (IEC Compliant)

Initial luminous flux 2700 lm

Init. Corr. colour temperature 3000 K

Application Conditions

Performance ambient temperature 25 °C

Tq

Suitable for random switching Not applicable

Product Data

Full product code 871869625545200

Order product name 4MX960 1 ST540C LED25S/830 PSU MB WH

EAN/UPC – product 8718696255452

Order code 25545200


Numerator – quantity per pack 1

Numerator – packs per outer box 1

Material no. (12NC) 910500456570

Net weight (piece) 1.700 kg

Dimensional drawing



Maxos LED spot inserts 4MX960

