



EcoStyle

ST440T LED39S/830 PSU MB WH

EcoStyle track mounting, LED Module, system flux 3500 lm, 830 warm white, Power supply unit (On/Off), Medium beam, Safety class II, White

Retailers are looking for an affordable LED accent-lighting solution with a reasonable payback compared to conventional technologies. Now, thanks to EcoStyle, they need look no further. With a LED light source and dedicated reflector system, EcoStyle delivers powerful, good-quality accent lighting, enabling retailers to display their merchandise in the best possible light. For food and fashion retailers, EcoStyle is available with special light recipes to further enhance the store ambiance and to show the produce and goods on offer in the very best light: Fresh Food Champagne is the perfect LED solution for displaying fruit, vegetables, cheese, bread and pastries in a warm lighting ambiance; Fresh Food Meat creates the best light setting for meat enhancement in a cool natural ambiance; CrispWhite is the clear choice for fashion retailers to make colors appear rich and intense while keeping whites bright. The track-mounted EcoStyle is also available in a choice of black or white finish. And the combination of efficient LED technology and an innovative heatsink ensures that this is a reliable, lasting solution.

Product data

General Information		
Lamp family code	LED35S [LED Module, system flux 3500 lm]	
Light source replaceable	No	
Number of gear units	Unit	
Driver included	Yes	
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Product family code	ST440T [EcoStyle track mounting]	
Lighting Technology	LED	
CE mark	Yes	
Warranty period	5 years	

Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	3,900 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	123.80952380952381 lm/W
Colour rendering index (CRI)	80
Beam angle of light source	120 degree(s)
Light source colour	830 warm white
Optic type	Medium beam
Optical cover type	Acrylic bowl/cover clear
Luminaire light beam spread	22°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.25 ms
Power Consumption	31.5 W
Power Factor (Fraction)	0.95
Connection	-
Cable	-
Number of products on MCB of 16 A type B	34

Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate

Optical cover/lens material	Polymethyl methacrylate
Fixation material	Polyamide
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	230 mm
Overall width	112 mm
Overall height	194 mm
Dimensions (height x width x depth)	194 x 112 x 230 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	No

Product Data

Order product name	ST440T LED39S/830 PSU MB WH
Full product name	ST440T LED39S/830 PSU MB WH
Full EOC	871869625934400
Order code	25934400
Material no. (12 NC)	910500456865
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696259344
Numerator – packs per outer box	1
EAN/UPC – Case	8718696259344

Dimensional drawing

