



StyliD CrispWhite

ST730T LED12S/CRW PSE MB WH-BK

STYLID MINI G3 TRACK, LED module, system flux 1200 lm, Crisp white, Power supply unit, DC compatible for central emergency lighting, Medium beam, White and black

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain high-quality lighting to catch the customer's eye, as well as flexibility in architectural integration. Fashion retailers generally want superior light sources that illuminate fabrics in the truest way possible, making colors appear rich and intense while keeping whites bright. A warm color temperature is often preferred, as it keeps colors true and saturated. Until now, a drawback of LED has been that whites can appear yellowish. The good news – that's about to change. CrispWhite is a unique concept in retail lighting that makes whites appear whiter than white, yet still gives colors a warm and saturated intensity. This new color experience will wow customers and make merchandise impossible to resist.

Product data

General Information			
Lamp family code	LED12S [LED module, system flux 1200 lm]	B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Cap-Base	- [-]	Product family code	ST730T [STYLID MINI G3 TRACK]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	1 unit	CE mark	Yes
Gear	-	Warranty period	5 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 30 s
		EU RoHS compliant	Yes

StyliD CrispWhite

Light Technical	
Luminous Flux	1,200 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	81 lm/W
Color rendering index (CRI)	≥95
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	Crisp white
Optic type	Medium beam
Optical cover type	-
Luminaire light beam spread	30°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	14 A
Inrush time	0.25 ms
Power Consumption	14.8 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24
Temperature	
Ambient temperature range	+10 to +40 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit, DC compatible for central emergency lighting
Constant light output	No
Mechanical and Housing	
Housing Material	Metal–Plastic
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polymethyl methacrylate
Fixation material	-

Housing Color	White and black
Optical cover finish	Clear
Overall length	258 mm
Overall width	73 mm
Overall height	159 mm
Dimensions (Height x Width x Depth)	159 x 73 x 258 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.39) SDCM <3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80
Application Conditions	
Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes
Product Data	
Order product name	ST730T LED12S/CRW PSE MB WH-BK
Full product name	ST730T LED12S/CRW PSE MB WH-BK
Full product code	871869626369300
Order code	910500457101
Material Nr. (12NC)	910500457101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696263693
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696263693

StyliD CrispWhite

Dimensional drawing

