



LuxSpace Accent Mini

RS731B LED12S/930 PSE-E NB WH

LuxSpace Accent Mini G3, LED Module, system flux 1100 lm, 930 warm white, Power supply unit DC compatible, external, Narrow beam, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, LuxSpace Accent is the ideal energy-efficient solution for today's demanding retail environments, covering a wide variety of lighting applications, including CrispWhite for fashion stores and Food recipes for supermarkets.

Product data

General Information			
Lamp family code	LED11S [LED Module, system flux 1100 lm]	Product family code	RS731B [LuxSpace Accent Mini G3]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	1 unit	Value ladder	Specification
Driver included	Yes	CE mark	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Warranty period	5 years
Service tag	Yes	Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 30 s
		EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	1,200 lm

LuxSpace Accent Mini

Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	114 lm/W
Color rendering index (CRI)	≥90
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	930 warm white
Optic type	Narrow beam
Optical cover type	Clear glass
Luminaire light beam spread	18°
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	4.4 A
Inrush time	20 ms
Power Consumption	13.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector with 2 poles and pull relief
Cable	-
Number of products on MCB of 16 A type B	30

Temperature

Ambient temperature range	+10 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit DC compatible, external
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	-

Fixation material	-
Housing Color	White
Optical cover finish	Clear
Overall height	86 mm
Overall diameter	105 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.434, 0.403) SDCM <2
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	RS731B LED12S/930 PSE-E NB WH
Full product name	RS731B LED12S/930 PSE-E NB WH
Full product code	871869684759600
Order code	84759600
Material Nr. (12NC)	910500457283
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696847596
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696847596

LuxSpace Accent Mini

Dimensional drawing

