



# LuxSpace Accent Mini

## RS731B LED12S/930 PSE-E MB WH

LuxSpace Accent Mini G3, LED module, system flux 1200 lm, 930 warm white, Power supply unit DC compatible, external, Medium beam, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, LuxSpace Accent is the ideal energy-efficient solution for today's demanding retail environments, covering a wide variety of lighting applications

### Product data

General Information		Lighting Technology	
Lamp family code	LED12S [LED module, system flux 1200 lm]	Value ladder	Specification
Light source replaceable	No	CE mark	Yes
Number of gear units	1 unit	Warranty period	5 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
Service tag	Yes	Glow-wire test	Temperature 650 °C, duration 30 s
Product family code	RS731B [LuxSpace Accent Mini G3]	EU RoHS compliant	Yes
Light Technical			
Luminous Flux	1,200 lm		
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	133 lm/W		

## LuxSpace Accent Mini

Color rendering index (CRI)	≥90
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	930 warm white
Optic type	Medium beam
Optical cover type	-
Luminaire light beam spread	24°
Unified glare rating CEN	Not applicable

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	4.4 A
Inrush time	20 ms
Power Consumption	12.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector with 2 poles and pull relief
Cable	-
Number of products on MCB of 16 A type B	30

### Temperature

Ambient temperature range	+10 to +35 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit DC compatible, external
Control interface	-
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	-
Fixation material	-

Housing Color	White
Optical cover finish	Clear
Overall height	86 mm
Overall diameter	105 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.434, 0.403) SDCM <2
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80


### Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

### Product Data

Order product name	RS731B LED12S/930 PSE-E MB WH
Full product name	RS731B LED12S/930 PSE-E MB WH
Full product code	871869684766400
Order code	910500457290
Material Nr. (12NC)	910500457290
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696847664
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696847664

## Dimensional drawing



## LuxSpace Accent Mini

