



# StyliD

## ST730T LED12S/830 PSD-VLC WB BK

STYLID MINI G3 TRACK, LED module, system flux 1200 lm, 830 warm white, Power supply unit with DALI interface, DC compatible for central emergency lighting (integrated), Wide beam, Black

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, StyliD is the ideal energy-efficient solution for today's demanding retail environments, covering a variety of lighting applications, with including CrispWhite for fashion stores and Food recipes for supermarkets. StyliD family features full passive cooling for the complete range that allows faster payback in the Performance size as well.

### Product data

General Information		
Lamp family code	LED12S [LED module, system flux 1200 lm]	maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	
Light source replaceable	No	
Number of gear units	1 unit	
Gear	-	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen	
Product family code	ST730T [STYLID MINI G3 TRACK]	
Lighting Technology	LED	
CE mark	Yes	
Warranty period	5 years	
Flammability mark	For mounting on normally flammable surfaces	
ENEC mark	ENEC mark	
Glow-wire test	Temperature 650 °C, duration 30 s	

EU RoHS compliant	Yes
-------------------	-----

#### Light Technical

Luminous Flux	1,200 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	114.28571428571429 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	Wide beam
Optical cover type	-
Luminaire light beam spread	36°

#### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	16 A
Inrush time	0.22 ms
Power Consumption	10.2 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

#### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible for central emergency lighting (integrated)
Control interface	DALI
Constant light output	No

#### Mechanical and Housing

Housing Material	Metal-Plastic
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polymethyl methacrylate

Fixation material	-
Housing Color	Black
Optical cover finish	Clear
Overall length	279 mm
Overall width	73 mm
Overall height	171 mm
Dimensions (Height x Width x Depth)	171 x 73 x 279 mm

#### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

#### Product Data

Order product name	ST730T LED12S/830 PSD-VLC WB BK
Full product name	ST730T LED12S/830 PSD-VLC WB BK
Full product code	871869684825800
Order code	910500457348
Material Nr. (12NC)	910500457348
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696848258
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696848258

## Dimensional drawing

