



StyliD

ST740C LED27S/830 PSU WB WH

STYLID COMPACT G3 SURFACE, LED Module, system flux 2700 lm, 830 warm white, Power supply unit, DC-compatible for central emergency lighting, Wide beam, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, StyliD is the ideal energy-efficient solution for today's demanding retail environments, covering a variety of lighting applications, with including CrispWhite for fashion stores and Food recipes for supermarkets.

Product data

General Information			
Lamp family code	LED27S [LED Module, system flux 2700 lm]	useful life (B50) value also represents the B10 value.	
Cap base	- [-]	Product family code	ST740C [STYLID COMPACT G3 SURFACE]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	Unit	CE mark	Yes
Gear	-	Warranty period	5 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median	ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 30 s
		EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	2,700 lm

Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	120 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	830 warm white
Optic type	Wide beam
Optical cover type	-
Luminaire light beam spread	34°

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	14.5 A
Inrush time	0.22 ms
Power Consumption	22.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	32

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit, DC-compatible for central emergency lighting
Constant light output	No

Mechanical and Housing

Housing material	Metal-Plastic
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Polyamide
Housing Colour	White
Optical cover/lens finish	Clear

Overall length	218 mm
Overall width	89 mm
Overall height	179 mm
Dimensions (height x width x depth)	179 x 89 x 218 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	ST740C LED27S/830 PSU WB WH
Full product name	ST740C LED27S/830 PSU WB WH
Full EOC	871869684837100
Order code	84837100
Material no. (12 NC)	910500457360
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696848371
Numerator – packs per outer box	1
EAN/UPC - Case	8718696848371

Dimensional drawing



