



# StyliD

## ST740T LED27S/827 PSD-VLC WB WH LIN

STYLID COMPACT G3 TRACK, LED Module, system flux 2700 lm, 827 warm white, Power supply unit with DALI interface, DC-compatible for central emergency lighting (integrated), Wide beam, Linear-lens array oval shape, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, StyliD is the ideal energy-efficient solution for today's demanding retail environments, covering a variety of lighting applications, with including CrispWhite for fashion stores and Food recipes for supermarkets.

### Product data

General Information			
Lamp family code	LED27S [LED Module, system flux 2700 lm]	Product family code	ST740T [STYLID COMPACT G3 TRACK]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	Unit	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 30 s
		EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	2,750 lm
		Correlated Colour Temperature	2700 K

Luminous efficacy (rated) (nom.)	122.2222222222223 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	827 warm white
Optic type	Wide beam
Optical cover type	Linear-lens array oval shape
Luminaire light beam spread	30° x 60°

#### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	5.3 A
Inrush time	0.70 ms
Power Consumption	22.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

#### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC-compatible for central emergency lighting (integrated)
Control interface	DALI
Constant light output	No

#### Mechanical and Housing

Housing material	Metal-Plastic
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Clear

Overall length	279 mm
Overall width	89 mm
Overall height	191 mm
Dimensions (height x width x depth)	191 x 89 x 279 mm

#### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.45, 0.41) SDCM <3
Power consumption tolerance	+/-10%

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

#### Product Data

Order product name	ST740T LED27S/827 PSD-VLC WB WH LIN
Full product name	ST740T LED27S/827 PSD-VLC WB WH LIN
Full EOC	871869684845600
Order code	84845600
Material no. (12 NC)	910500457368
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696848456
Numerator – packs per outer box	1
EAN/UPC - Case	8718696848456

Dimensional drawing

