



StyliD

ST750T LED39S/830 PSD-VLC VWB WH

STYLID PERFORMANCE G3 TRACK, LED Module, system flux 3900 lm, 830 warm white, Power supply unit with DALI interface, DC compatible for central emergency lighting (integrated), Very wide beam, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer’s eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, StyliD is the ideal energy-efficient solution for today’s demanding retail environments, covering a variety of lighting applications, with including CrispWhite for fashion stores and Food recipes for supermarkets. StyliD family features full passive cooling for the complete range that allows faster payback in the Performance size as well.

Product data

General Information		
Lamp family code	LED39S [LED Module, system flux 3900 lm]	the median useful life (B50) value also represents the B10 value.
Light source replaceable	No	
Number of gear units	1 unit	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore,	
Product family code	ST750T [STYLID PERFORMANCE G3 TRACK]	
Lighting Technology	LED	
CE mark	Yes	
Warranty period	5 years	
Flammability mark	For mounting on normally flammable surfaces	
ENEC mark	ENEC mark	
Glow-wire test	Temperature 650 °C, duration 30 s	
EU RoHS compliant	Yes	

Light Technical	
Luminous Flux	3,900 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	123.80952380952381 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	Very wide beam
Optical cover type	-
Luminaire light beam spread	54°
Unified glare rating CEN	Not applicable

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	5.3 A
Inrush time	0.70 ms
Power Consumption	31.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature	
Ambient temperature range	+10 to +40 °C

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible for central emergency lighting (integrated)
Control interface	DALI
Constant light output	No

Mechanical and Housing	
Housing Material	Metal-Plastic
Reflector material	Aluminum
Optic material	Polycarbonate
Optical cover material	Polymethyl methacrylate

Fixation material	-
Housing Color	White
Optical cover finish	Clear
Overall length	322 mm
Overall width	119 mm
Overall height	251 mm
Dimensions (Height x Width x Depth)	251 x 119 x 322 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data	
Order product name	ST750T LED39S/830 PSD-VLC VWB WH
Full product name	ST750T LED39S/830 PSD-VLC VWB WH
Full product code	871869684856200
Order code	910500457379
Material Nr. (12NC)	910500457379
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696848562
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696848562

Dimensional drawing

