



CoreLine Downlight

DN130B LED10S/830 PSED-E II WH

CoreLine Downlight WH, LED Module, system flux 1000 lm, 830 warm white, Power supply unit with DALI interface, DC-compatible, external, Safety class II, Wide beam, Acrylic bowl/cover frosted, DC operated central emergency lighting, Plug-in connector 3-pole Wago, White

The CoreLine Downlight range of recessed luminaires is designed to replace CFL-ni/CFL-i based downlight luminaires. Their attractive TCO helps customers to make the switch to LED. These luminaires create a natural lighting effect for use in general lighting applications. They also deliver instant energy savings and have a much longer lifetime, creating a real value-for-money and environmentally friendly solution. They are easy to install thanks to their standard cut-out size and push-in connectors.

Product data

General Information		Product family code	DN130B [CoreLine Downlight WH]
Lamp family code	LED10S [LED Module, system flux 1000 lm]	Lighting Technology	LED
Light source replaceable	No	Value ladder	Performance
Number of gear units	Unit	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.		
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	-
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	Yes

CoreLine Downlight

Light Technical	
Luminous Flux	1,100 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	100 lm/W
Colour rendering index (CRI)	80
Beam angle of light source	120 degree(s)
Light source colour	830 warm white
Optic type	Wide beam
Optical cover type	Acrylic bowl/cover frosted
Luminaire light beam spread	90°
Unified Glare Rating (CEN)	28
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	20.4 A
Inrush time	195 ms
Power Consumption	11 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 3-pole Wago
Cable	-
Number of products on MCB of 16 A type B	24
Temperature	
Ambient temperature range	-10 to +40 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC-compatible, external
Control interface	DALI
Constant light output	No
Mechanical and Housing	
Housing material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Aluminium
Optical cover/lens material	Polycarbonate

Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Frosted
Overall height	99 mm
Overall diameter	166 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L70
Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes
Product Data	
Order product name	DN130B LED10S/830 PSED-E II WH
Full product name	DN130B LED10S/830 PSED-E II WH
Full EOC	871869685223100
Order code	85223100
Material no. (12 NC)	910500457701
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696852231
Numerator – packs per outer box	1
EAN/UPC - Case	8718696852231

CoreLine Downlight

Dimensional drawing

