



CoreLine Downlight

DN130B LED20S/840 PSED-E II WH

CoreLine Downlight WH, LED Module, system flux 2000 lm, 840 neutral white, Power supply unit with DALI interface, DC-compatible, external, Safety class II, White

The CoreLine Downlight range of recessed luminaires is designed to replace CFL-ni/CFL-i based downlight luminaires. Their attractive TCO helps customers to make the switch to LED. These luminaires create a natural lighting effect for use in general lighting applications. They also deliver instant energy savings and have a much longer lifetime, creating a real value-for-money and environmentally friendly solution. They are easy to install thanks to their standard cut-out size and push-in connectors.

Product data

General Information		Value ladder		Performance	
Lamp family code	LED20S [LED Module, system flux 2000 lm]	CE mark	Yes	Warranty period	5 years
Light source replaceable	No	Flammability mark	For mounting on normally flammable surfaces	ENEC mark	-
Number of gear units	Unit	Glow-wire test	Temperature 850 °C, duration 5 s	EU RoHS compliant	Yes
Driver included	Yes	Light Technical			
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	Luminous Flux	2,100 lm	Correlated Colour Temperature	4000 K
Product family code	DN130B [CoreLine Downlight WH]	Luminous efficacy (rated) (nom.)	95 lm/W	Colour rendering index (CRI)	80
Lighting Technology	LED	Beam angle of light source	120 degree(s)		

CoreLine Downlight

Light source colour	840 neutral white
Optic type	Wide beam
Optical cover type	Acrylic bowl/cover frosted
Luminaire light beam spread	90°
Unified Glare Rating (CEN)	28

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	20.4 A
Inrush time	195 ms
Power Consumption	22 W
Power Factor (Fraction)	0.95
Connection	Plug-in connector 3-pole Wago
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC-compatible, external
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Aluminium
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Frosted

Overall height	109 mm
Overall diameter	216 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.37) SDCM <5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L70


Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	DN130B LED20S/840 PSED-E II WH
Full product name	DN130B LED20S/840 PSED-E II WH
Full EOC	871869685272900
Order code	85272900
Material no. (12 NC)	910500457727
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696852729
Numerator – packs per outer box	1
EAN/UPC – Case	8718696852729

Dimensional drawing



CoreLine Downlight

