



# CoreLine Downlight

## DN130B LED10S/830 PSED-E IP44 II WH

CoreLine Downlight WH, LED Module, system flux 1000 lm, 830 warm white, Power supply unit with DALI interface, DC compatible, external, Safety class II, Wire-protected, splash-proof, White

CoreLine Downlight delivers on the CoreLine promise of innovative, easy to use and high-quality recessed downlights. The CoreLine Downlight range is suitable for one-to-one conventional luminaire replacements, with an attractive TCO that helps customers to make the switch to LED. These recessed downlights create uniform light distribution for use in general lighting applications. They also deliver instant energy savings and have a much longer lifetime, creating a real value-for-money and environmentally-friendly solution. CoreLine DN140B recessed downlights are easy to install thanks to their standard cut-out size and push-in connectors. An InterAct Ready option with integrated wireless communications is available in this family, which can be used with InterAct gateways, sensors and software.

### Product data

General Information			
Lamp family code	LED10S [LED Module, system flux 1000 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source replaceable	No	Product family code	DN130B [CoreLine Downlight WH]
Number of gear units	1 unit	Lighting Technology	LED
Driver included	Yes	Value ladder	Performance
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	-
		Glow-wire test	Temperature 850 °C, duration 5 s

# CoreLine Downlight

EU RoHS compliant	Yes
<b>Light Technical</b>	
Luminous Flux	1,100 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	Wide beam
Optical cover type	Acrylic bowl/cover frosted
Luminaire light beam spread	90°
Unified glare rating CEN	28
<b>Operating and Electrical</b>	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	20.4 A
Inrush time	195 ms
Power Consumption	11 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 3-pole Wago
Cable	-
Number of products on MCB of 16 A type B	24
<b>Temperature</b>	
Ambient temperature range	-10 to +40 °C
<b>Controls and Dimming</b>	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible, external
Control interface	DALI
Constant light output	No
<b>Mechanical and Housing</b>	
Housing Material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Aluminum

Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Frosted
Overall height	99 mm
Overall diameter	166 mm
<b>Approval and Application</b>	
Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <5
Power consumption tolerance	+/-10%
<b>Over Time Performance (IEC Compliant)</b>	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L70
<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes
<b>Product Data</b>	
Order product name	DN130B LED10S/830 PSED-E IP44 II WH
Full product name	DN130B LED10S/830 PSED-E IP44 II WH
Full product code	871869687883500
Order code	910500458080
Material Nr. (12NC)	910500458080
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696878835
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696878835

## CoreLine Downlight

### Dimensional drawing

