



StoreFlux gen3 rim

GD602B LED27S/830 PSU-E MB WH-WH

StoreFlux3, LED Module, system flux 2700 lm, 830 warm white, Power supply unit external (On/Off), Medium beam, White and white

The StoreFlux gridlight can be equipped with up to four LED modules with a special reflector system to deliver top-quality light that makes your shop and merchandise look great. The combination of multiple LED sources with high lumen packages in one luminaire creates sparkling light effects. StoreFlux offers low maintenance compared with CDM and high efficiency compared to halogen.

Warnings and Safety

- The luminaire should be mounted outside of arm's reach. Manipulating the product when hot is only possible with an insulated glove
- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements
- All photometrical data is calculated without optional front glass. Flux should be reduced by 3.5% when using a front glass
- In case of no front glass lens, cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For areas with high levels of dust, the use of the optional front glass is strongly advised, as it can then be easily cleaned with a (dry) microfiber cloth
- For multi-spot configurations, please use single configuration photometry and duplicate it as per the number of spots in given configuration.

Product data

General Information		Remarks
Lamp family code	LED27S [LED Module, system flux 2700 lm]	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example
Light source replaceable	No	
Number of gear units	2 units	
Driver included	Yes	

StoreFlux gen3 rim

	B10. Therefore, the median useful life (B50) value also represents the B10 value.
Service tag	Yes
Product family code	GD602B [StoreFlux3]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	5,400 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	120 lm/W
Color rendering index (CRI)	≥80
Number of light sources	2
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	Medium beam
Optical cover type	Acrylic toothed
Luminaire light beam spread	24°
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.25 ms
Power Consumption	23.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	34

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White and white
Optical cover finish	Clear
Overall length	326 mm
Overall width	179 mm
Overall height	165 mm
Dimensions (Height x Width x Depth)	165 x 179 x 326 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	No

Product Data

Order product name	GD602B LED27S/830 PSU-E MB WH-WH
Full product name	GD602B LED27S/830 PSU-E MB WH-WH
Full product code	871869688118700
Order code	88118700
Material Nr. (12NC)	910500458194
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696881187
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696881187

StoreFlux gen3 rim

Dimensional drawing

