



GreenSpace Accent Projector Gen1

ST320T LED19S/FMT PSU MB WH

GREENSPACE ACCENT PROJECTOR - LED module 1900 lm - Fresh meat - Power supply unit - Medium beam - White

Thanks to the GreenSpace Accent family, retailers and building operators can now make the switch from CDM to LED and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Projector’s regular 3C adaptor and specific lumen packages make retrofit installation quick and easy. For fashion and food retailers, the GreenSpace Accent Projector is available with special light flavours and LED recipes to show the clothes and fresh food produce on offer in the very best light. Check out our Fashion and Food catalogue pages to find out more about CrispWhite, PremiumWhite, Fresh Food Meat and Fresh Food Champagne.

Product data

General Information		Luminaire light beam spread	
Number of light sources	1 [1 pc]	Connection	No [-]
Lamp family code	LED19 [LED module 1900 lm]	Cable	-
Beam angle of light source	120 °	Protection class IEC	Safety class II (II)
Light source colour	Fresh meat	Mounting	3C-69 [3-circuit power track adapter GA69 (connection point) for XTS and XTSE tracks]
Cap base	- [-]	Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Light source replaceable	No	Flammability mark	F [For mounting on normally flammable surfaces]
Number of gear units	1 unit	CE mark	CE mark
Driver/power unit/transformer	PSU [Power supply unit]	ENEC mark	ENEC mark
Driver included	Yes	UL mark	-
Optic type	MB [Medium beam]		
Optical cover/lens type	PM [PMMA bowl/cover]		

GreenSpace Accent Projector Gen1

Warranty period	5 years
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB (16 A type B)	50
EU RoHS compliant	Yes
Product family code	ST320T [GREENSPACE ACCENT PROJECTOR]
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Average CLO power consumption	- W
Inrush current	12.8 A
Inrush time	208 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Polyamide
Optical cover/lens finish	Clear
Overall length	182 mm
Overall width	114 mm
Overall height	193 mm
Colour	White

Dimensions (height x width x depth)	193 x 114 x 182 mm (7.6 x 4.5 x 7.2 in)
-------------------------------------	---

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	1900 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	86 lm/W
Init. Corr. Colour Temperature	3000 K
Init. Colour rendering index	≥85
Initial chromaticity	(0.40, 0.33) SDCM<3
Initial input power	22 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Ambient temperature range	+10 to +40 °C
Performance ambient temperature Tq	25 °C
Suitable for random switching	No


Product Data

Full product code	871869916648900
Order product name	ST320T LED19S/FMT PSU MB WH
EAN/UPC – product	8718699166489
Order code	16648900
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910500459366
SAP net weight (piece)	0.980 kg




GreenSpace Accent Projector Gen1

Dimensional drawing




GreenSpace Accent ST315T-ST330T


Photometric data




OFPC1_ST320T1xLED19SFMTMBLIN



IFPC1_ST320T1xLED19SFMTMB




IFAS1_ST320T1xLED19SFMTMB




IFAS1_ST320T1xLED19SFMTMBLIN

GreenSpace Accent Projector Gen1

Photometric data



IFCC1_ST320T1xLED19SFMTMBLIN



IFCC1_ST320T1xLED19SFMTMB

