



GreenSpace Accent Projector Gen1

ST320T LED19S/FMT PSU MB WH

GREENSPACE ACCENT PROJECTOR, LED module 1900 lm, Fresh meat, Power supply unit (On/Off), Medium beam, White

Thanks to the GreenSpace Accent family, retailers and building operators can now make the switch from CDM to LED and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Projector's regular 3C adaptor and specific lumen packages make retrofit installation quick and easy. For fashion and food retailers, the GreenSpace Accent Projector is available with special light flavours and LED recipes to show the clothes and fresh food produce on offer in the very best light. Check out our Fashion and Food catalogue pages to find out more about CrispWhite, PremiumWhite, Fresh Food Meat and Fresh Food Champagne.

Product data

General Information			
Lamp family code	LED19 [LED module 1900 lm]	useful life (B50) value also represents the B10 value.	
Cap base	- [-]	Product family code	ST320T [GREENSPACE ACCENT PROJECTOR]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	Unit	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median	Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 5 s

GreenSpace Accent Projector Gen1

EU RoHS compliant	Yes
-------------------	-----

Light Technical

Luminous Flux	1,900 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	86 lm/W
Colour rendering index (CRI)	≥85
Beam angle of light source	120 degree(s)
Light source colour	Fresh meat
Optic type	Medium beam
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	30°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Average CLO power consumption	- W
Inrush current	12.8 A
Inrush time	208 ms
Power Consumption	22 W
Power Factor (Fraction)	0.9
Connection	-
Cable	-
Number of products on MCB of 16 A type B	50

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polymethyl methacrylate

Fixation material	Polyamide
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	182 mm
Overall width	114 mm
Overall height	193 mm
Dimensions (height x width x depth)	193 x 114 x 182 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.40, 0.33) SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	No

Product Data

Order product name	ST320T LED19S/FMT PSU MB WH
Full product name	ST320T LED19S/FMT PSU MB WH
Full EOC	871869916648900
Order code	16648900
Material no. (12 NC)	910500459366
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699166489
Numerator – packs per outer box	1
EAN/UPC – Case	8718699166489

GreenSpace Accent Projector Gen1

Dimensional drawing

