



GreenSpace Accent Projector Gen1

ST320T LED17S/840 PSU MB WH

GREENSPACE ACCENT PROJECTOR, LED module 1700 lm, 840 neutral white, Power supply unit (On/Off), Medium beam, White

Thanks to the GreenSpace Accent family, retailers and building operators can now make the switch from CDM to LED and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Projector's regular 3C adaptor and specific lumen packages make retrofit installation quick and easy. For fashion and food retailers, the GreenSpace Accent Projector is available with special light flavours and LED recipes to show the clothes and fresh food produce on offer in the very best light. Check out our Fashion and Food catalogue pages to find out more about CrispWhite, PremiumWhite, Fresh Food Meat and Fresh Food Champagne.

Product data

General Information		
Lamp family code	LED17 [LED module 1700 lm]	
Cap base	- [-]	
Light source replaceable	No	
Number of gear units	Unit	
Driver included	Yes	
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Product family code		ST320T [GREENSPACE ACCENT PROJECTOR]
Lighting Technology		LED
CE mark		Yes
Warranty period		5 years
Flammability mark		For mounting on normally flammable surfaces
ENEC mark		ENEC mark
Glow-wire test		Temperature 650 °C, duration 5 s

GreenSpace Accent Projector Gen1

EU RoHS compliant	Yes
-------------------	-----

Light Technical

Luminous Flux	1,800 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	125 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	840 neutral white
Optic type	Medium beam
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	24°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220–240 V
Line Frequency	50 to 60 Hz
Inrush current	18.6 A
Inrush time	0.240 ms
Power Consumption	14.4 W
Power Factor (Fraction)	0.9
Connection	-
Cable	-
Number of products on MCB of 16 A type B	32

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Polyamide

Housing Colour	White
Optical cover/lens finish	Clear
Overall length	182 mm
Overall width	114 mm
Overall height	193 mm
Dimensions (height x width x depth)	193 x 114 x 182 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	ST320T LED17S/840 PSU MB WH
Full product name	ST320T LED17S/840 PSU MB WH
Full EOC	8718699166540000
Order code	16654000
Material no. (12 NC)	910500459372
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699166540
Numerator – packs per outer box	1
EAN/UPC - Case	8718699166540

GreenSpace Accent Projector Gen1

Dimensional drawing

