



# GreenSpace Accent Projector Gen1

## ST320T LED39S/830 PSU VWB BK

GREENSPACE ACCENT PROJECTOR, LED module 3900 lm, 830 warm white, Power supply unit (On/Off), Very wide beam, Black

Thanks to the GreenSpace Accent family, retailers and building operators can now make the switch from CDM to LED and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Projector's regular 3C adaptor and specific lumen packages make retrofit installation quick and easy. For fashion and food retailers, the GreenSpace Accent Projector is available with special light flavours and LED recipes to show the clothes and fresh food produce on offer in the very best light. Check out our Fashion and Food catalogue pages to find out more about CrispWhite, PremiumWhite, Fresh Food Meat and Fresh Food Champagne.

### Product data

General Information			
Lamp family code	LED39 [LED module 3900 lm]	Therefore, the median useful life (B50) value also represents the B10 value.	
Cap base	- [-]	Product family code	ST320T [GREENSPACE ACCENT PROJECTOR]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	Unit	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10.	Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 5 s
		EU RoHS compliant	Yes

# GreenSpace Accent Projector Gen1

<b>Light Technical</b>	
Luminous Flux	3,900 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	123.80952380952381 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	830 warm white
Optic type	Very wide beam
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	54°
Unified Glare Rating (CEN)	Not applicable
<b>Operating and Electrical</b>	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.260 ms
Power Consumption	31.5 W
Power Factor (Fraction)	0.9
Connection	-
Cable	-
Number of products on MCB of 16 A type B	20
<b>Temperature</b>	
Ambient temperature range	+10 to +40 °C
<b>Controls and Dimming</b>	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No
<b>Mechanical and Housing</b>	
Housing material	Aluminium
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Polyamide
Housing Colour	Black

Optical cover/lens finish	Clear
Overall length	182 mm
Overall width	114 mm
Overall height	193 mm
Dimensions (height x width x depth)	193 x 114 x 182 mm
<b>Approval and Application</b>	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM<3
Power consumption tolerance	+/-10%
<b>Over Time Performance (IEC Compliant)</b>	
Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80
<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes
<b>Product Data</b>	
Order product name	ST320T LED39S/830 PSU VWB BK
Full product name	ST320T LED39S/830 PSU VWB BK
Full EOC	871869916671700
Order code	16671700
Material no. (12 NC)	910500459389
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699166717
Numerator – packs per outer box	1
EAN/UPC - Case	8718699166717

# GreenSpace Accent Projector Gen1

## Dimensional drawing

