



GreenSpace Accent Projector Gen1

ST320T LED39S/830 PSU WB SI

GREENSPACE ACCENT PROJECTOR, LED module 3900 lm, 830 warm white, Power supply unit (On/Off), Wide beam, Silver

Thanks to the GreenSpace Accent family, retailers and building operators can now make the switch from CDM to LED and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Projector's regular 3C adaptor and specific lumen packages make retrofit installation quick and easy. For fashion and food retailers, the GreenSpace Accent Projector is available with special light flavours and LED recipes to show the clothes and fresh food produce on offer in the very best light. Check out our Fashion and Food catalogue pages to find out more about CrispWhite, PremiumWhite, Fresh Food Meat and Fresh Food Champagne.

Product data

General Information			
Lamp family code	LED39 [LED module 3900 lm]	Therefore, the median useful life (B50) value also represents the B10 value.	
Cap base	- [-]	Product family code	ST320T [GREENSPACE ACCENT PROJECTOR]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	Unit	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10.		
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 5 s
		EU RoHS compliant	Yes

GreenSpace Accent Projector Gen1

Light Technical	
Luminous Flux	3,900 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	123.80952380952381 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	830 warm white
Optic type	Wide beam
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	34°
Unified Glare Rating (CEN)	Not applicable
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.260 ms
Power Consumption	31.5 W
Power Factor (Fraction)	0.9
Connection	-
Cable	-
Number of products on MCB of 16 A type B	20
Temperature	
Ambient temperature range	+10 to +40 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No
Mechanical and Housing	
Housing material	Aluminium
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Polyamide
Housing Colour	Silver

Optical cover/lens finish	Clear
Overall length	182 mm
Overall width	114 mm
Overall height	193 mm
Dimensions (height x width x depth)	193 x 114 x 182 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM<3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80
Application Conditions	
Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes
Product Data	
Order product name	ST320T LED39S/830 PSU WB SI
Full product name	ST320T LED39S/830 PSU WB SI
Full EOC	871869916674800
Order code	16674800
Material no. (12 NC)	910500459392
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699166748
Numerator – packs per outer box	1
EAN/UPC - Case	8718699166748

GreenSpace Accent Projector Gen1

Dimensional drawing

