



LuxSpace Accent CrispWhite

RS751B LED39S/CRW PSE-E WB WH

LuxSpace Accent CrispWhite, 60 W, 3900 lm, 3000 K, Wide beam, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain high-quality lighting to catch the customer's eye, as well as flexibility in architectural integration. Fashion retailers generally want superior light sources that illuminate fabrics in the truest way possible, making colours appear rich and intense while keeping whites bright. A warm colour temperature is often preferred, as it keeps colours true and saturated. Until now, a drawback of LED has been that whites can appear yellowish. The good news – that's about to change. CrispWhite is a unique concept in retail lighting that makes whites appear whiter than white, yet still gives colours a warm and saturated intensity. This new colour experience will wow customers and make merchandise impossible to resist.

Product data

General Information			
Lamp family code	LED39S [LED Module, system flux 3900 lm]		useful life (B50) value also represents the B10 value.
Light source replaceable	No	Product family code	RS751B [LuxSpace Accent Performance G3]
Number of gear units	Unit	Lighting Technology	LED
Driver included	Yes	CE mark	Yes
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median	Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 5 s

LuxSpace Accent CrispWhite

EU RoHS compliant	Yes
-------------------	-----

Light Technical

Luminous Flux	3,900 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	65 lm/W
Colour rendering index (CRI)	≥95
Beam angle of light source	120 degree(s)
Light source colour	Crisp white
Optic type	Wide beam
Optical cover type	-
Luminaire light beam spread	30°

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W W
Average CLO power consumption	- W W
Inrush current	23.5 A
Inrush time	0.272 ms
Power Consumption	60 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit DC-compatible, external
Control interface	-
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	Aluminium
Optic material	Polycarbonate

Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Clear
Overall height	150 mm
Overall diameter	168 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.39) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	RS751B LED39S/CRW PSE-E WB WH
Full product name	RS751B LED39S/CRW PSE-E WB WH
Full EOC	871869916711000
Order code	16711000
Material no. (12 NC)	910500459422
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699167110
Numerator – packs per outer box	1
EAN/UPC - Case	8718699167110

Dimensional drawing

