



# LuxSpace Accent

## RS752B LED49S/840 PSED-VLC-E VWB WH

LuxSpace Accent, 40 W, 5150 lm, 4000 K, DALI, Very wide beam, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, LuxSpace Accent is the ideal energy-efficient solution for today's demanding retail environments, covering a wide variety of lighting applications, including CrispWhite for fashion stores and Food recipes for supermarkets.

### Product data

General Information			
Light source replaceable	No	CE mark	Yes
Number of gear units	Unit	Warranty period	5 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
Product family code	RS752B [LuxSpace Accent Performance G3]	Glow-wire test	Temperature 650 °C, duration 5 s
Lighting Technology	LED	EU RoHS compliant	Yes
Value ladder	Specification	Light Technical	
		Luminous Flux	5,150 lm
		Correlated Colour Temperature	4000 K
		Luminous efficacy (rated) (nom.)	129 lm/W
		Colour rendering index (CRI)	≥80
		Beam angle of light source	120 degree(s)

## LuxSpace Accent

Light source colour	840 neutral white
Optic type	Very wide beam
Optical cover type	-
Luminaire light beam spread	54°

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	5.3 A
Inrush time	0.7 ms
Power Consumption	40 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	30

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC-compatible, external
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing material	Aluminium
Reflector material	Aluminium
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	231 mm
Overall width	168 mm

Overall height	126 mm
Overall diameter	168 mm
Dimensions (height x width x depth)	126 x 168 x 231 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

### Product Data

Order product name	RS752B LED49S/840 PSED-VLC-E VVB WH
Full product name	RS752B LED49S/840 PSED-VLC-E VVB WH
Full EOC	871869916740000
Order code	16740000
Material no. (12 NC)	910500459451
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699167400
Numerator – packs per outer box	1
EAN/UPC - Case	8718699167400

Dimensional drawing

