



# LuxSpace Accent Fresh Food

## RS751B LED19S/ROSE PSE-E WB WH

LuxSpace Accent Fresh Food, 22.5 W, 1900 lm, 2200 K, Wide beam, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain high-quality lighting to catch the customer's eye, as well as flexibility in architectural integration. Food retailers generally want superior light sources that illuminate their fresh food counters in the freshest way possible, making food appealing while keeping the light ambiance attractive and welcoming. When a warm light ambiance is preferred, Fresh Food Champagne is the perfect LED solution to light fruit, vegetables, cheese, bread and pastries. Fresh Food Rose is a perfect warm-light solution for meat counters, enhancing the redness of meat but also slowing down the discoloration of sliced meat. When a brighter or more natural light ambiance is preferred, Fresh Food Authentic White is recommended for fruits, vegetables, cheeses, bread and pastries. Fresh Food Meat creates the best light setting for meat enhancement in a cooler ambiance.

### Product data

General Information		
Lamp family code	LED19S [LED module, system flux 1900 lm]	maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source replaceable	No	
Number of gear units	1 unit	
Driver included	Yes	Product family code
Remarks	*-Per Lighting Europe guidance paper	RS751B [LuxSpace Accent Performance G3]
	"Evaluating performance of LED based luminaires - January 2018": statistically there	Lighting Technology
	is no relevant difference in lumen	LED
		Value ladder
		Specification
		CE mark
		Yes
		Warranty period
		5 years

# LuxSpace Accent Fresh Food

Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

## Light Technical

Luminous Flux	1,900 lm
Correlated Color Temperature (Nom)	2200 K
Luminous Efficacy (rated) (Nom)	84 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	Rosé
Optic type	Wide beam
Optical cover type	-
Luminaire light beam spread	41°

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	32 A
Inrush time	0.25 ms
Power Consumption	22.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	12

## Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit DC compatible, external
Control interface	-
Constant light output	No

## Mechanical and Housing

Housing Material	Aluminum
------------------	----------

Reflector material	Aluminum
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Frosted
Overall height	150 mm
Overall diameter	168 mm

## Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.48, 0.38)
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

## Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

## Product Data

Order product name	RS751B LED19S/ROSE PSE-E WB WH
Full product name	RS751B LED19S/ROSE PSE-E WB WH
Full product code	871869916745500
Order code	16745500
Material Nr. (12NC)	910500459456
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699167455
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699167455

LuxSpace Accent Fresh Food

Dimensional drawing

